




Fitting- and operating aids	Pos.	Type to discontinued Available till	Order no.
	<b>Push-type grease gun</b>		
	Push-type grease gun with pointed nozzle	31.12.2009	384356
	<p>Push-grease gun with follow-up piston as per DIN 1282 and pointed nozzle for funnel lubrication nipple DIN 3405. This gun has an overall length of 170 mm and a capacity of 60 ccm and is suitable for the lubrication of recirculating ball bearing guides, for example.</p>		
	<b>One-hand grease gun LUB-1</b>		
	LUB-1 one-hand high pressure grease gun with LUB-1-TR needle-shaped pointed nozzle	647958	
	<p>Robust and ergonomic design for manual greasing. For use with lubricating greases and mineral oils. The LUB-1-TR needle-shaped pointed nozzle is suitable for cup head lubricating nipples in accordance with DIN 3405, miniature cup head lubricating nipples and lubricating holes. For example for greasing recirculating ball bearing guides or ball screws in the following products: DGE, DGEA, DGC, EGC, SLG, EGSP/K etc. The grease gun is filled manually via the filling nozzle with the help of a filling device. It's vented via an exhaust valve.</p>		
	<p>Volumetric capacity: 120 ccm<sup>3</sup>            Delivery rate: 0.5 cm<sup>3</sup>/stroke            Operating pressure: 400 bar            Weight when empty: 660 g            Length without pipe: 230 mm            Barrel diameter and length: Ø40 x 140 mm            Connecting thread nozzle: M10x1            Connecting thread nozzle pipe: G1/8"</p>		
	<b>Accessories for the grease gun LUB-1</b>		
	LUB-1-KU greasing adapter (M10x1 internal thread) for EGSK-20/-26/-33 electrical slides	744166	
	LUB-1-KE greasing adapter (M10x1 internal thread) for the EGSK-46 electrical slide	744167	
<p>LUB-1-KU and LUB-1-KE greasing adapters can be attached to the LUB-1 one-hand grease gun in place of the LUB-1-TR needle-shaped nozzle. The LUB-1-KU greasing adapter is suitable for ball type lubricating nipples similar to those specified in DIN 3402. These are used in EGSK-20/-26/-33 electrical slides. The LUB-1-KE greasing adapter is suitable for taper lubricating nipples similar to those specified in DIN 71412. These are used in the EGSK-46 electrical slide. The LUB-1-TR needle-shaped pointed nozzle must be used for the EGSK-15 electrical slide.</p>			
LUB-1-TR-L greasing adapter (Nozzle tube dia. 6 x 200 axial)	647959		
LUB-1-TR-L greasing adapter (Nozzle tube dia. 6 x 200 transverse)	647960		
<p>These nozzle tubes can be screwed onto the one-hand grease gun LUB-1 647958 and are ideal for the lubrication of <b>very difficult</b> to access locations.</p>			
<b>Mounting sleeve</b>			
Mounting sleeve 1/8"	VL-5-1/8, MFH-5-1/8	228389	
Mounting sleeve 1/4"	VL-5-1/4, MFH-5-1/4	229363	
<b>Screwdriver</b>			
M3, Slotted screwdriver (DIN 546) ADVUL-12/16	384353		
M4, Slotted screwdriver (DIN 546) ADVUL-20-...-40	384354		
M5, Slotted screwdriver (DIN 546) ADVUL-50-...-100	384355		